

PRC03 Connector Included Cable

Cables supporting more devices are available through the website!!

PRC0312 Connector Support Model Number Table

Shape Specification	Number of Cores	CN1	Component Page	CN2	Component Page	
P PT	2	PRC03-12A10-2AM10.5	298			
	3	PRC03-12A10-3AM10.5	298			
	4	PRC03-12A10-4M10.5	298			
	5	PRC03-12A10-5M10.5	298			
	7	PRC03-12A10-7M10.5	298			
	S ST	2	PRC03-12A10-2AF10.5	298		
		3	PRC03-12A10-3AF10.5	298		
4		PRC03-12A10-4F10.5	298			
5		PRC03-12A10-5F10.5	298			
7		PRC03-12A10-7F10.5	298			
PP	2	PRC03-12A10-2AM10.5	298	PRC03-12A10-2AM10.5	298	
	3	PRC03-12A10-3AM10.5	298	PRC03-12A10-3AM10.5	298	
	4	PRC03-12A10-4M10.5	298	PRC03-12A10-4M10.5	298	
	5	PRC03-12A10-5M10.5	298	PRC03-12A10-5M10.5	298	
	7	PRC03-12A10-7M10.5	298	PRC03-12A10-7M10.5	298	
SS	2	PRC03-12A10-2AF10.5	298	PRC03-12A10-2AF10.5	298	
	3	PRC03-12A10-3AF10.5	298	PRC03-12A10-3AF10.5	298	
	4	PRC03-12A10-4F10.5	298	PRC03-12A10-4F10.5	298	
	5	PRC03-12A10-5F10.5	298	PRC03-12A10-5F10.5	298	
	7	PRC03-12A10-7F10.5	298	PRC03-12A10-7F10.5	298	
PS	2	PRC03-12A10-2AM10.5	298	PRC03-12A10-2AF10.5	298	
	3	PRC03-12A10-3AM10.5	298	PRC03-12A10-3AF10.5	298	
	4	PRC03-12A10-4M10.5	298	PRC03-12A10-4F10.5	298	
	5	PRC03-12A10-5M10.5	298	PRC03-12A10-5F10.5	298	
	7	PRC03-12A10-7M10.5	298	PRC03-12A10-7F10.5	298	
PY	2	PRC03-12A10-2AM10.5	298	F1.25-3.5	468	
	3	PRC03-12A10-3AM10.5	298	F1.25-3.5	468	
	4	PRC03-12A10-4M10.5	298	F1.25-3.5	468	
	5	PRC03-12A10-5M10.5	298	F1.25-3.5	468	
	7	PRC03-12A10-7M10.5	298	F1.25-3.5	468	
SY	2	PRC03-12A10-2AF10.5	298	F1.25-3.5	468	
	3	PRC03-12A10-3AF10.5	298	F1.25-3.5	468	
	4	PRC03-12A10-4F10.5	298	F1.25-3.5	468	
	5	PRC03-12A10-5F10.5	298	F1.25-3.5	468	
	7	PRC03-12A10-7F10.5	298	F1.25-3.5	468	
RP RPT RPRT	2	PRC03-21A10-2AM	299			
	3	PRC03-21A10-3AM	299			
	4	PRC03-21A10-4M	299			
	5	PRC03-21A10-5M	299			
	7	PRC03-21A10-7M	299			
RS RST RSRT	2	PRC03-21A10-2AF	299			
	3	PRC03-21A10-3AF	299			
	4	PRC03-21A10-4F	299			
	5	PRC03-21A10-5F	299			
7	PRC03-21A10-7F	299				

PRC0332 Connector Support Model Number Table

Shape Specification	Number of Cores	CN1	Component Page	CN2	Component Page	
JP JPT	2	PRC03-32A10-2AM10.5	298			
	3	PRC03-32A10-3AM10.5	298			
	4	PRC03-32A10-4M10.5	298			
	5	PRC03-32A10-5M10.5	298			
	7	PRC03-32A10-7M10.5	298			
	JS JST	2	PRC03-32A10-2AF10.5	298		
		3	PRC03-32A10-3AF10.5	298		
4		PRC03-32A10-4F10.5	298			
5		PRC03-32A10-5F10.5	298			
7		PRC03-32A10-7F10.5	298			
JPP	2	PRC03-32A10-2AM10.5	298	PRC03-12A10-2AM10.5	298	
	3	PRC03-32A10-3AM10.5	298	PRC03-12A10-3AM10.5	298	
	4	PRC03-32A10-4M10.5	298	PRC03-12A10-4M10.5	298	
	5	PRC03-32A10-5M10.5	298	PRC03-12A10-5M10.5	298	
	7	PRC03-32A10-7M10.5	298	PRC03-12A10-7M10.5	298	
JSS	2	PRC03-32A10-2AF10.5	298	PRC03-12A10-2AF10.5	298	
	3	PRC03-32A10-3AF10.5	298	PRC03-12A10-3AF10.5	298	
	4	PRC03-32A10-4F10.5	298	PRC03-12A10-4F10.5	298	
	5	PRC03-32A10-5F10.5	298	PRC03-12A10-5F10.5	298	
	7	PRC03-32A10-7F10.5	298	PRC03-12A10-7F10.5	298	
JPS	2	PRC03-32A10-2AM10.5	298	PRC03-12A10-2AF10.5	298	
	3	PRC03-32A10-3AM10.5	298	PRC03-12A10-3AF10.5	298	
	4	PRC03-32A10-4M10.5	298	PRC03-12A10-4F10.5	298	
	5	PRC03-32A10-5M10.5	298	PRC03-12A10-5F10.5	298	
	7	PRC03-32A10-7M10.5	298	PRC03-12A10-7F10.5	298	
JSP	2	PRC03-32A10-2AF10.5	298	PRC03-12A10-2AM10.5	298	
	3	PRC03-32A10-3AF10.5	298	PRC03-12A10-3AM10.5	298	
	4	PRC03-32A10-4F10.5	298	PRC03-12A10-4M10.5	298	
	5	PRC03-32A10-5F10.5	298	PRC03-12A10-5M10.5	298	
	7	PRC03-32A10-7F10.5	298	PRC03-12A10-7M10.5	298	
JPY	2	PRC03-32A10-2AM10.5	298	F1.25-3.5	468	
	3	PRC03-32A10-3AM10.5	298	F1.25-3.5	468	
	4	PRC03-32A10-4M10.5	298	F1.25-3.5	468	
	5	PRC03-32A10-5M10.5	298	F1.25-3.5	468	
	7	PRC03-32A10-7M10.5	298	F1.25-3.5	468	
JSY	2	PRC03-32A10-2AF10.5	298	F1.25-3.5	468	
	3	PRC03-32A10-3AF10.5	298	F1.25-3.5	468	
	4	PRC03-32A10-4F10.5	298	F1.25-3.5	468	
	5	PRC03-32A10-5F10.5	298	F1.25-3.5	468	
	7	PRC03-32A10-7F10.5	298	F1.25-3.5	468	
JPJP	2	PRC03-32A10-2AM10.5	298	PRC03-32A10-2AM10.5	298	
	3	PRC03-32A10-3AM10.5	298	PRC03-32A10-3AM10.5	298	
	4	PRC03-32A10-4M10.5	298	PRC03-32A10-4M10.5	298	
	5	PRC03-32A10-5M10.5	298	PRC03-32A10-5M10.5	298	
	7	PRC03-32A10-7M10.5	298	PRC03-32A10-7M10.5	298	
JSJS	2	PRC03-32A10-2AF10.5	298	PRC03-32A10-2AF10.5	298	
	3	PRC03-32A10-3AF10.5	298	PRC03-32A10-3AF10.5	298	
	4	PRC03-32A10-4F10.5	298	PRC03-32A10-4F10.5	298	
	5	PRC03-32A10-5F10.5	298	PRC03-32A10-5F10.5	298	
	7	PRC03-32A10-7F10.5	298	PRC03-32A10-7F10.5	298	
JPJS	2	PRC03-32A10-2AM10.5	298	PRC03-32A10-2AF10.5	298	
	3	PRC03-32A10-3AM10.5	298	PRC03-32A10-3AF10.5	298	
	4	PRC03-32A10-4M10.5	298	PRC03-32A10-4F10.5	298	
	5	PRC03-32A10-5M10.5	298	PRC03-32A10-5F10.5	298	
	7	PRC03-32A10-7M10.5	298	PRC03-32A10-7F10.5	298	

Connector Included Cable Selection Method

Square Connector Included Cable

Coaxial Connector Included Cable

Round Connector Included Cable

Nylon Connector Included Cable

Custom Service

Connector Included Cable Documents