

Clamp Plates for Inspection Components

L Pins / T Pins

■ Features: Clamp plates for clamping inspection components and panel parts to set reference positions.

■ Edge Shape Selectable

KJCLPS

Material: S45C

RoHS10

Part Number Type	L	H	Selection				W 0.1mm Increment	Unit Price
			T	M	D	N		
KJCLPS	40	15	5	10	5	10	When T=10 0~7	
			10					
	60	20	5	15	7	20		
			10					
80	15 20 30	10		(N>D)	25			
			30					

■ Straight Edge

KJCLP

Material: S45C

RoHS10

Part Number Type	L	H	Selection				W 0.1mm Increment	Unit Price
			T	M	D	N		
KJCLP	40	15	10	5	15	25	When T=10 0~7	
	60			7				
	80	15 20 30		(N>D)	30			
			35					

Ordering Example

Part Number - H - B - T - M - D - N - W

KJCLPS40 - H15 - B5 - T10 - M5 - D10 - N25 - W2.0

KJCLP60 - H20 - T10 - M7 - D15 - N30 - W3.0

■ L Pins

Type	Material	Surface Treatment	Hardness
KJL	Handle (d dim.) SGD3	Electroless Nickel Plating	23~33HRC
KJLB	Pin (D dim.) S45CF	Black Oxide	

KJL KJLB

KJLSB

Material: S45C

RoHS10

■ T Pins

Type	Material	Surface Treatment	Hardness
KJTSB	Handle (d dim.) SGD3 Pin (D dim.) S45CF	Black Oxide	23~33HRC

KJTSB

Material: S45C

RoHS10

Part Number Type	D	d	Unit Price			
			L Pin	T Pin		
KJL KJLB KJLSB KJTSB	6	7	KJL	KJLB	KJLSB	KJTSB
	8	9				
	10	11				

Ordering Example

Part Number

KJL6

KJTSB8