


Stationary Lever



Type	Lever		Handle
	Material	Surface Treatment	Material
C-LRGN	Carbon Steel for Mechanical Structure	Chrome Plating	ABS



Part Number		L		Handle Color	L1	d	D	H	W	Reference Mass (g)
Type	M									
C-LRGN	8	83	101 121	Black	12	10	22	42	8	75
	10	125	150		14	12	25	50	10	135
	12	132	156		16	16	32	60	13	245



Ordering Example
Part Number - L
C-LRGN8 - 83


Part Number		L	Unit Price
Type	M		
C-LRGN	8	83	
		101	
		121	
	10	125	
		150	
	12	132	
		156	

Revolving Handles




Type	Handle		Screw	
	Material	Surface Treatment	Material	Surface Treatment
C-GRMS	Carbon Steel for Mechanical Structure	Chrome Plating	Carbon Steel for Mechanical Structure	Chrome Plating
C-GRMSS	Carbon Steel for Mechanical Structure	Chrome Plating	Carbon Steel for Mechanical Structure	Black Oxide

C-GRMS
(Left Photo)



C-GRMSS
(Right Photo)



Part Number		D	d	H	L	W	A	Reference Mass (g)	Unit Price
Type	M								
C-GRMS	8	18	13	63	14	10	8	120	
	10	22	15	80	16	13	10	210	
	12	25	18	100	18	16	12	355	
C-GRMSS	6	16	6	50	12	5	12	65	
	8	18	8	63	14	6	12	115	
	10	22	10	80	16	8	12	195	




Ordering Example
Part Number
C-GRMS8

Revolving Handle with Hex Socket



Type	Handle		Thread	
	Material	Surface Treatment	Material	Surface Treatment
C-GRW	Phenol	Carbon Steel for Mechanical Structure	Trivalent Chromate	



Part Number		H	D	d	W	L	Mass (g)	Unit Price
Type	M (Coarse)							
C-GRW	8	63	19	14.5	3	16	40	
	10	80	26	20	4	18	96	
	12	100	28	22	5	22	135	



Ordering Example
Part Number - H
C-GRW8 - 63

How to Mount

