

**NEW**

HOT WATER HOSES

HOSE CUTTER

# RUBBER HOSE FOR HOT WATER / HOSE CUTTER

— HEAT RESISTANT 100°C —

■ Application Use for cooling mold.

■ Rubber Hose for Hot Water  
-Heat Resistant of 100°C-  
**M-CHN**



■ Features

- Use for cooling mold.
- Select from 2 colors (red and blue) according to the application. Convenient for distinguishing between IN and OUT.

**M** Material : NBR  
Usable temperature range : ~100°C  
Max. usable pressure : 2.068MPa (300psi)

No.	Outer dia.	Inner dia.	Min. bending radius
10	16.7	9.5	76.2
13	19.1	12.7	127.7
19	26.2	19.1	152.4

Part Number		Color	L (m)	Unit Price		
Type	No.			No.		
				10	13	19
			1			
			2			
			3			
			4			
			5			
			6			
			7			
			8			
			9			
			10			
			11			
			12			
			13			
			14			
		R (Red)	15			
			16			
		L (Blue)	17			
			18			
			19			
			20			
			21			
			22			
			23			
			24			
			25			
			26			
			27			
			28			
			29			
			30			

**M-CHN**

10  
13  
19

R (Red)  
L (Blue)

Quotation



Order

Part Number	Color	L
M-CHN 10	R	3
M-CHN 19	L	21



Days to Ship

Quotation



Price

Quotation

■ Hose Cutter  
**M-HCUT**



■ Features

- Cuts mold cooling hoses safely and at a right angle.
- It can also cut resin pipes such as PVC, PE and PB.

Part Number	M Blade material	S Blade coating
M-HCUT-25	Steel	Teflon
M-HCUT-38		
M-HCUT-50	Stainless steel	—

Width	Length	Applicable hose outer dia.	Applicable pipe outer dia. (PVC/PE/PB)	Part Number	Unit Price
31	210	25	25	M-HCUT-25	
	220	38	30	M-HCUT-38	Quotation
	245	50	38	M-HCUT-50	



Order

Part Number
M-HCUT-25
M-HCUT-38



Days to Ship

Quotation



Price

Quotation