


**NEW**

**TUBES  
TUBE**

shows in red

**T-CHPU** RoHS 10



Type	Material
T-CHPU	Polyester

Outer× Inner dia.	Min. bending radius (mm)	Burst pressure (MPa)	Usable pressure (MPa)	Usable temperature range (°C)	Part Number		Tube color	Total length L (m)	Unit Price 1~30 pcs
					Type	No.			
4x2.5	10	3.2	0~1.0	0~50	T-CHPU	0425	B (black) OR (orange) BU (blue) W (white) Y (yellow) G (green) R (red)	20	Quotation
								30	
6x4	16	2.7				0640		40	
								50	
								20	
								30	
								40	
								50	

For quantities not displayed here, refer to our MISUMI website for more information.



Order

Part Number — Tube color — Total length L  
T-CHPU0425 — R — 20



Days to Ship

**Quotation**



Price

**Quotation**

**M-UD** RoHS 10



Outer× Inner dia.	Min. bending radius (mm)	Burst pressure (MPa)	Usable pressure (MPa)	Usable temperature range (°C)	Part Number		Tube color	Total length L (m)	Unit Price
					Type	No.			
4x2.5	8	1.2	0.4	-15~50°C	M-UD		C (Transparent)	5	Quotation
6x4	12							10	
8x6	27	0.75	0.3					20	
10x7.5	34							100	
12x9	38								

**■ Features**

The ultra-soft tubing is ideal for oscillating parts. For example, in vacuum piping and around the actuator.



Order

Part Number — Tube color — Total length L  
M-UD0425 — C — 5



Days to Ship

**Quotation**



Price

**Quotation**

REMOVAL  
RELATED PRODUCTS