

Pull Handles with Caps / Nylon Pull Handles

Aluminum Tube Pull Handles

Nylon Pull Handles with Caps

UPCDG
(Nylon 6)

*Easier mounting is possible by the combination use with the Nuts for Handles below.

Material
Glass Fiber Reinforced Nylon 6

Part Number Type	L	L1	Allowable Load (N)	Unit Price	
				Mass (g)	
UPCDG	90	133	500	30	
	94	136.5		33	
	117	160		36	
	132	175		39	

Pull Handles with Caps

Type	Handle		Cap	
	Material	Surface Treatment	Material	Color
HHDG	ADC12	Baked Finish	ABS	White
HHDGS	SUS304 Equivalent	Buffed Finish	ABS	White

*Easier mounting is possible by the combination use with the Nuts for Handles below.

Countersink for M5

Part Number Type	L	Mass (g)	Set of applicable Screws and Nuts	Unit Price	
				Screw	Quantity
HHDG HHDGS	100	62	Flat Head Screw M5	2	HHDG
					HHDGS

Ordering Example

Part Number
UPCDG90
HHDG100

Nuts for Pull Handles

HHPUW

Material: SUS304

Part Number Type	P	B	A	M	Handle	Unit Price	Volume Discount Rate
	100	12	110	5	HHDG100		

Ordering Example

Part Number
HHPUW90

Nylon Pull Handles

UPFN

Material
Handle: Glass Fiber Reinforced Nylon 6
Threaded Section: Brass (Insert)

Part Number Type	A	L	Color of Handle	L1	H	h	M (Coarse)	Allowable Load (N)	Mass (g)	Unit Price		
										B (Black)	W (White)	M (Orange), R (Red)
UPFN	26	105	B (Black)	121	37	29	6	500	55			
		110	W (White)						60			
		117	M (Orange) R (Red)						62			

*The default color of handle will be black unless specified.

Ordering Example

Part Number - L - Color of Handle
UPFN26 - 105 - B

Aluminum Tube Pull Handles - Small Diameter

UWAPNC
UWAPFC (L Configurable Type)

UHFAPC
UHFAPFC (L Configurable Type)

Material
Tube: A6063
Elbow: Polycarbonate

Part Number Type	L	Set of applicable Screws and Nuts	Unit Price	
			UWAPNC	UHFAPC
UWAPNC UHFAPC	100	Hex Socket Head Cap Screw M6		
	150			
	200			
	250			
	300			

Part Number Type	L 1mm Increment	Set of applicable Screws and Nuts	Unit Price	
			UWAPFC	UHFAPFC
UWAPFC UHFAPFC	100~150	Hex Socket Head Cap Screw M6		
	151~200			
	201~250			
	251~300			

Ordering Example

Part Number
UWAPNC200
UWAPFC-237

*For L Dimensions, add "-" (hyphen).

Aluminum Tube Pull Handles

UWAPN
UWAPF (L Configurable Type)

UHFAPN
UHFAPF (L Configurable Type)

Material
Tube: A6063
Elbow: Glass Fiber Reinforced Nylon

Part Number Type	L	Set of applicable Screws and Nuts	Unit Price	
			UWAPN	UHFAP
UWAPN UHFAP	150	Flat Head Screw M8		
	200			
	250			
	300			
	400			
	500			
	600			

Part Number Type	L 1mm Increment	Set of applicable Screws and Nuts	Unit Price	
			UWAPF	UHFAPF
UWAPF UHFAPF	100~150	Flat Head Screw M8		
	151~200			
	201~250			
	251~300			
	301~400			
	401~500			
	501~600			

Ordering Example

Part Number
UWAPN150
UHFAPF-185

*For L Dimensions, add "-" (hyphen).