

# Recessed Stainless Steel Grip Handles

# Recessed Folding Pull Handles / Recessed TPE / Plastic Grip Handles

**Recessed Grip Handles** **UWUANA**

Threaded Type

Panel Mounting Hole Dimensions

Countersink

Panel Mounting Hole Dimensions

Material: SUS304

RoHS10

Part Number Type	Threaded, Countersink	Mass (g)	Unit Price 1 ~ 9 pc (s)	Volume Discount Rate 10~49	Volume Discount Rate 50~200
UWUANA	B (Threaded)	85 (Threaded)			
	S (Countersink)	94 (Countersink)			

Ordering Example: Part Number **UWUANA** - Type Selection **B**

**Recessed Grip Handles** **UWUAN**

Threaded Studs Type

Nut Type

Panel Mounting Hole Dimensions

Material: SUS304, Finish: Brushed

RoHS10

Part Number Type	Threaded Studs Type	Nut Type	W	P	F	S	A	A1	T	(J)	L1	W1	Mass (g)	Unit Price
UWUAN	94	B (Threaded Studs Type)	60	76	32	61	25	43	12	14.5	63	45	80	
	109.5	N (Nut Type)	64	88	38	67.5	25	40	14.5	13	73	42	100	
	138		88	110	65	96	35	62	21	11.5	99	64	170	

Ordering Example: Part Number **UWUAN94** - Threaded Studs Type **B** - Nut Type **B**

**Recessed Grip Handles** **UWAUNS**

Panel Mounting Hole Dimensions

Material: SUS304, Finish: Brushed, Accessory: Nut 2 pcs., Washer 2 pcs., SUS304

RoHS10

Example

Part Number Type	L	P	S	L1	L2	Mass (g)	Unit Price
UWAUNS	90	74	58	61	60	30	
	120	100	86	91	90	50	

Ordering Example: Part Number **UWAUNS120**

**Recessed Folding Pull Handles** **UWUAFN**

Panel Mounting Hole Dimensions

Material: ADC12

Part Number Type	L	W	P	F	S	A	G	L1	W1	Mass (g)	Unit Price
UWUAFN	130	91	118	79	109	69	49.5	110	70	197	
	200	80	184	50	169	71	51	171	73	286	

**Recessed TPE Grip Handles** **UWAUNB**

Panel Mounting Hole Dimensions

Material: Non-PVC TPE

\* TPE is thermoplastic elastomer, which has properties close to rubber at ambient temperature.

5 pcs./pkg. Order quantity should be noted. Adhesive is recommended for mounting.

Part Number Type	L	W	L1	W1	A	S	F	F2	t	t1	L2	W2	R	Mass (g)	Unit Price (5 pcs./pkg.)
UWAUNB	62	34	40	18	44	29	23	53	4	18	54	24	11.5	30	
	92	42	62	22	66	42	27	83	5	32	84	28	13.5	50	
	133	58	92	30	96	47	39	119	6	35	120	40	19.5	110	

**Recessed Plastic Grip Handles** **UWAUNJ**

Panel Mounting Hole Dimensions

Material: ABS Resin

The thickness of the applicable plate is 1 ~ 1.2 mm.

Adhesive is recommended for mounting.

Example

Part Number Type	L	W	L2	W2	A	Mass (g)	Unit Price
UWAUNJ	80	60	70	48.5	69	50	
	120	82	108.5	70	108	70	
	180	82	168.5	70	168	90	

Ordering Example: Part Number **UWUAFN130**, **UWAUNB92**, **UWAUNJ80**