

Note that, for some of the types shown here, order might be unable to be received by the MISUMI Malaysia, Indonesia and/or India offices.

Resin Washers / Resin Washer Bulk Packages

Standard / Dimension Configurable

When you need large quantities, Bulk Packages are more economical.

Pkg.	Type		Material	Color
	Dimension Selectable	Dimension Configurable		
PACK-WSJJ	WSJJ	FWSJJ	Polyacetal	White
-	WSJK	FWSJK		Black
PACK-WSJM	WSJM	FWSJM	MC Nylon Standard Grade	Blue
-	WSJW	FWSJW		Ivory
-	WSJD	FWSJD	MC Nylon Conductive Grade	Black
-	WSJT	FWSJT		CDR2 CDR6
-	WSJB	FWSJB	Bakelite	Paper Base Natural Color
-	WSJN	FWSJN		Cloth Base Natural Color
-	WSJF	FWSJF	Fluororesin	White
-	WSJP	FWSJP	PEEK	Gray
-	WSJE	FWSJE	Epoxy Glass	Green

Material Properties P.141

Sold by the package 1 package contains 10 pieces.

Part Number	Type	D	V Selection	T Selection	PACK-WSJJ				PACK-WSJM				
					Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate			
					1 ~ 4 pkg(s).	5-9	10-19	20-30	1 ~ 4 pkg(s).	5-9	10-19	20-30	
PACK-WSJJ PACK-WSJM	4	2		2									
	5	2 3		2									
	6	2 3 4		2									
	8	3 4 5 6	2 3 5										
	10	3 4 5 6 8	2 3 5										
	12	4 5 6 8	2 3										
	15	6 8 10 12	2 3										
	20	6 8 10 12	2 3 5										

For package, minimum order unit is 1 pack. For orders of 31 or more identical packages, please request a quotation.

Ordering Example

Part Number - V - T

PACK-WSJJ4 - 2 - 2

Dimension Selectable

Part Number	Type	D	V Selection	T Selection	Unit Price																			
					WSJJ WSJK	WSJM WSJW	WSJD	WSJT	WSJB	WSJN	WSJF	WSJP	WSJE											
WSJJ WSJK WSJM WSJW WSJD WSJT WSJB WSJN WSJF WSJP WSJE	4	2		2																				
	5	2 3		2																				
	6	2 3 4		2																				
	8	2 3 4 5 6	2 3 5																					
	10	2 3 4 5 6 8	2 3 5																					
	12	3 4 5 6 8 10	2 3 5																					
	13	4 5 6 8 10	2 3 5																					
	14	4 5 6 8 10	2 3 5																					
	15	4 5 6 8 10 12	2 3 5																					
	16	4 5 6 8 10 12	2 3 5																					
	20	4 5 6 8 10 12 15 16	2 3 5																					
	25	6 8 10 12 15 16 20	2 3 5																					
	30	8 10 12 15 16 20 25	2 3 5																					
	35	10 12 15 16 20 25	3 5 10																					
	40	10 12 15 16 20 25 30	3 5 10																					
	50	10 12 15 16 20 25 30	3 5 10																					
60	15 16 20 25 30	3 5 10																						

Ordering Example

Part Number - V - T

WSJJ6 - 4 - 2

Dimension Configurable

No specification available for those without value.

Part Number	D	V	T	Unit Price																				
				FWSJJ FWSJK	FWSJM FWSJW	FWSJD	FWSJT	FWSJB	FWSJN	FWSJF	FWSJP	FWSJE												
FWSJJ FWSJK FWSJM FWSJW FWSJD FWSJT FWSJB FWSJN FWSJF FWSJP FWSJE	4.0-10 (0.5mm Increment)	0.5mm Increment (V3 or More)	0.5mm Increment	2.0- 5.0																				
	10.5-20 (0.5mm Increment)			5.5-10																				
	21-30 (1mm Increment)			2.0- 5.0																				
	31-40 (1mm Increment)			5.5-10																				
	41-50 (1mm Increment)			2.0- 5.0																				
	51-60 (1mm Increment)			5.5-10																				
	61-80 (1mm Increment)			2.0- 5.0																				
	81-100 (1mm Increment)			5.5-10																				

Ordering Example

Part Number - D - V - T

FWSJN - D10 - V5 - T5.5

Alterations

Part Number - D - V - T - (VKC, TKC)

WSJJ6 - 4 - 2 - VKC

FWSJM - D10 - V4 - T2 - TKC

Alterations are applicable to WSJJ, WSJM, FWSJJ and FWSJM only.

Alterations	I.D. Tolerance Change	Thickness Tolerance Change
Code	VKC	TKC
Spec.	Changes the I.D. tolerance to $+0.1$. Ordering Code VKC When $D \leq 50$, $D-V \geq 6$ When $51 \leq D \leq 80$, $D-V \geq 10$ When $81 \leq D \leq 100$, $D-V \geq 16$	Changes the Thickness Tolerance to ± 0.05 . Ordering Code TKC When $D \leq 50$, $D-V \geq 6$ When $D \leq 80$, $D-V \geq 10$ When $D \leq 100$, $D-V \geq 16$