


URETHANE SHEETS

URETHANE DIE PADS

RoHS



UT



T	±
1 ~ 4	±0.3
5 ~ 10	±0.4
15 ~ 25	±0.5
30 ~ 50	±1

Product guide P.1501

Shore A90

A	B	T	Catalog No.		Base unit price 1 ~ 9 pieces
			Type	T — A	
300	300	5	UT	5 — 300	Quotation
		6		6 — 300	
		8		8 — 300	
		10		10 — 300	
		15		15 — 300	
		20		20 — 300	
		25		25 — 300	
		30		30 — 300	
500	500	1	UT	1 — 500	
		2		2 — 500	
		3		3 — 500	
		4		4 — 500	
		5		5 — 500	
		6		6 — 500	
		8		8 — 500	
		10		10 — 500	
		15		15 — 500	
		20		20 — 500	
		25		25 — 500	
		30		30 — 500	
		50		50 — 500	

Order

Catalog No.
UT 8—500

Days to Ship

Quotation


Price

Quotation

RoHS



UTH (Configurable size type)



T	±
1 ~ 4	±0.3
5 ~ 10	±0.4
15 ~ 25	±0.5
30 ~ 50	±1

Product guide P.1501

Shore A90

Catalog No.		1mm increments		Catalog No.		1mm increments	
Type	T	A	B	Type	T	A	B
UTH	1	20 ~ 500	20 ~ 500	UTH	10	20 ~ 500	20 ~ 500
	2				15		
	3				20		
	4				25		
	5				30		
	6				40		
	8				50		

Order

Catalog No. — A — B
UTH 8 — 351 — 200

Days to Ship

Quotation


Price

Quotation

RoHS



UD



T	±
1 ~ 4	±0.3
5 ~ 10	±0.4
15 ~ 25	±0.5
30 ~ 50	±1

Product guide P.1501

Shore A90

A	B	L	T	Catalog No.			Base unit price
				Type	A — L	1 ~ 9 pieces	
25	25	50	±1	UD	25 —	50	Quotation
		100				100	
		300				300	
		500	+5 0			500	
		800				800	
		1000				1000	
50	50	50	±1	UD	50 —	50	
		100				100	
		300				300	
		500	+5 0			500	
		800				800	
		1000				1000	
75	50	50	±1	UD	75 —	50	
		100				100	
		300				300	
		500	+5 0			500	
		800				800	
		1000				1000	

Order

Catalog No.
UD 75—1000

Days to Ship

Quotation


Price

Quotation

RoHS



UDH (Configurable full length type)



L	±
25 ~ 200	+1 0
201 ~ 500	+2 0
501 ~ 1000	+3 0

Product guide P.1501

Shore A90

A	B	Catalog No.	L		Base unit price
		Type A	1mm increments		1 ~ 9 pieces
25	25	UDH 25	25 ~ 50		Quotation
			51 ~ 100		
			101 ~ 300		
			301 ~ 500		
			501 ~ 800		
			801 ~ 1000		
50	50	UDH 50	25 ~ 50		
			51 ~ 100		
			101 ~ 300		
			301 ~ 500		
			501 ~ 800		
			801 ~ 1000		
75	50	UDH 75	25 ~ 50		
			51 ~ 100		
			101 ~ 300		
			301 ~ 500		
			501 ~ 800		
			801 ~ 1000		

Order

Catalog No. — L
UDH 50 — 355

Days to Ship

Quotation

Price

Quotation