

LOCATING PILOT PINS

SLPS·SDST·SDKL were discontinued in 2017.

Male thread type RoHS

SLTL (Fixed P dimension)
SLTLH (Configurable P and B dimensions)

Ⓜ SKS93
ⓧ 37 ~ 43HRC

Ⓢ For SLTLH, (S) ≅ 1.6×P. ※1 SLTL6-SLTLH8→2 ※2 SLTL6-SLTLH8→2.5

The tip shape of SLTL is as shown above.

M×P	F	S	Catalog No. Type	P	B	Base unit price 1~9 pieces
5×0.8	12	10	(Fixed P dimension) SLTL	6	5 10	Quotation
6×1.0				8	5 10	
8×1.25				9	5 10	
10×1.5				10	5 10	
12×1.75	15	15	(Configurable P and B dimensions) SLTLH	12	10 15	Quotation
14				15 20		
15				15 20		
16×2.0	25	20		20	25 30	

Inlay male thread type RoHS

SLPS (Fixed P dimension)
SLPSH (Configurable P, B, and T dimensions)

Ⓜ SKS93
ⓧ 37 ~ 43HRC

Ⓢ For (s), s ≅ 1.6×P. ※1 D8→2 ※2 D8→2.5

The tip shape of SLPSH is shown above.

M×P	F	P	B	T	S	Catalog No. Type	D	Base unit price 1~9 pieces
6×1.0	12	6	3	10	(Fixed P dimension) SLPS	Quotation	8	Quotation
8×1.25	8	5	5	10				
12×1.75	15	10	17	13				
16×2.0	25	16	10	20				

Order

Catalog No. - P - B - T

SLTL 8 - B10

SLTLH 14 - P13.80 - B20

SLPSH 16 - P14.00 - B60 - T15

Days to Ship Quotation


Price Quotation

Alterations

Catalog No. - P - B - T - (SC)

SLPSH 10 - P8.50 - B10 - T3 - SC9

Alteration	Code	Spec.	1Code
	SC	Tip taper length change 8 < SC < S 1mm increments	Quotation



Female thread type RoHS

SNST (Fixed P dimension)
SNSTH (Configurable P and B dimensions)

Ⓜ SKS3
ⓧ 60 ~ 63HRC

Ⓢ For (s), s ≅ 1.6×P.

M×P	Catalog No. Type	P	B	Base unit price 1~9 pieces
4×0.7	(Fixed P dimension) SNST	6	10 15	Quotation
5×0.8		8	10 15	
6×1.0		12	15 20	
8×1.25		20	40 50	

Small head female thread type RoHS

SDST (Fixed P dimension)
SDSTH (Configurable P and B dimensions)

Ⓜ SKS3
ⓧ 60 ~ 63HRC

Dg6	M×P	P	L	S	B	Catalog No. Type	D	Base unit price 1~9 pieces
8	-0.005	5×0.8	6	15	6	(Fixed P dimension) SDST	8	Quotation
10	-0.014	6×1.0	8	8	8			
13	-0.006	8×1.25	10	20	12			
16	-0.017	10×1.5	12	17	10			

Small head one-side flat type RoHS

SDKL (Fixed P dimension)
SDKLH (Configurable P and B dimensions)

Ⓜ SKS3
ⓧ 60 ~ 63HRC

※SDKLH10→φ2.5

Dg6	P	B	Catalog No. Type	D	Base unit price 1~9 pieces
10	-0.005	6	(Fixed P dimension) SDKL	10	Quotation
13	-0.014	8		13	
16	-0.017	10		16	
20	-0.007	12		20	
25	-0.020	15		25	

Order


Catalog No. - P - B

SNST 8 - B10

SDSTH 13 - P11.48 - B28.0

Days to Ship Quotation

Price Quotation



LOCATING COMPONENTS FOR AUTOMOTIVE DIES