

HIGH PRECISION STRIPPER GUIDE BUSHINGS

— OIL TYPE/OIL-FREE TYPE —



The quantity discount rate is also applicable to alteration cost. All price & lead time are to be quoted.

Oil type

RoHS **VGBL** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
12	VGBL	8	10	13	16	20	Quotation
14		10	10	13	16	20 22 25	
18		13	13	16	20	22 25 30	
22		16	16	20	22 25 30 35		
25		20	20	22 25 30 35			
32		25	20 22 25 30 35				

RoHS **VGBH** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
12	VGBH	8	10	13	16	20	Quotation
14		10	10	13	16	20 22 25	
18		13	13	16	20	22 25 30	
22		16	16	20	22 25 30 35		
25		20	20	22 25 30 35			
32		25	20 22 25 30 35				

Oil-free type

RoHS **VGBZ** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
13	VGBZ	8	10	13	16	20	Quotation
16		10	10	13	16	20 22 25	
20		13	13	16	20	22 25 30	
24		16	16	20	22 25 30 35		
28		20	20	22 25 30 35			
34		25	20 22 25 30 35				

RoHS **VGHZ** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
13	VGHZ	8	10	13	16	20	Quotation
16		10	10	13	16	20 22 25	
20		13	13	16	20	22 25 30	
24		16	16	20	22 25 30 35		
28		20	20	22 25 30 35			
34		25	20 22 25 30 35				

Copper alloy oil type

RoHS **VSGSF** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
16	VSGSF	10	10	13	16	20	Quotation
20		13	13	16	20 25		
24		16	16	20 25 30			
28		20	20 25 30				

RoHS **VSGBF** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
16	VSGBF	10	10	13	16	20	Quotation
20		13	13	16	20 25		
24		16	16	20 25 30			
28		20	20 25 30				

Copper alloy oil-free type

RoHS **VSGCZ** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
16	VSGCZ	10	10	13	16	20	Quotation
20		13	13	16	20 25		
24		16	16	20 25 30			
28		20	20 25 30				
34		25	25 30				

RoHS **VSGFZ** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
16	VSGFZ	10	10	13	16	20	Quotation
20		13	13	16	20 25		
24		16	16	20 25 30			
28		20	20 25 30				
34		25	25 30				

Sintered alloy (dispersed solid lubricant) oil-free type

RoHS **VGBM** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
16	VGBM	10	10	13	16	20	Quotation
20		13	13	16	20 25		
24		16	16	20 25 30			
28		20	20 25 30				

RoHS **VGHM** (Loctite adhesive type)

D	CatalogNo.	L					U/Price
Type	d						Q'ty : 1-9
16	VGHM	10	10	13	16	20	Quotation
20		13	13	16	20 25		
24		16	16	20 25 30			
28		20	20 25 30				



CatalogNo. — L
VGBH10 — 16

Quantity discount rate

Quantity	1~9	10~19	20~49	50~100
Rate	—	5%	10%	15%



SGP Stock

- VGBL • VGBZ
- VGBH • VGHZ

5 Days Express T Express A P.i

For area out of Singapore please refer to P.i.

- VSG□F • VGBM
- VSG□Z • VGHM

5 Days Express A P.i

For area out of Singapore please refer to P.i.



CatalogNo. — L(C) — (DRC)
VGBH10 — LC12.5

5 Days Express service is not available
For area out of Singapore please refer to P.i.

Alteration	Changes dimension L (full length)		Machines groove for Loctite	
Code	LC		DRC	
Spec.	• VGBH • VGHM	• VGBL • VGBM	• Head type	• Straight type
Price	Quotation		Quotation	