


# Blocks for Adjusting Bolts

## Standard, Side Mounting, Side Mounting T Compact


■Features: Compact Type is available for limited spaces.

**Standard**



RoHS 10


Type		Material	Surface Treatment
H Selectable	H Configurable		
AJKC	AJKB	Steel for General Structure	Black Oxide
AJKCM	AJKBM		Electroless Nickel Plating
AJKCS	-	SUS304	-



Part Number	Type	No.	H										Unit Price								
			Selectable					Configurable 1mm Increment	d	H <sub>1</sub>	T	W	P	d <sub>2</sub>	d <sub>1</sub>	ℓ	L Selectable Type		H Configurable		
			AJKC	AJKCM	AJKCS	AJKB	AJKBM										AJLC	AJLCM	AJLB	AJLBM	
(H Selectable)	(H Configurable)	3	5	10	15	10~40	2.5	5	7	26	16	3.5	6	3.5							
		4	5	10	15		20	3.5	5	7	26	16	3.5	6	3.5						
		5	6	10	15		20	25	4.5	6	9	32	20	4.5	8	4.5					
		6	8	10	15		20	25	5.5	6	9	32	20	4.5	8	4.5					
		8	10	15	20		25	30	7.5	8	12	38	26	5.5	9.5	5.5					
		10		12	15	20	25	30	9.5	10	16	50	32								
		12		12	15	20	25	30	11.5				9	14	9						
		16		15	20	25	30	15.5	11	19	65	40									


Ordering Example Part Number - H  
AJKC6 - 8

**Side Mounting**



RoHS 10


Type		Material	Surface Treatment
H Selectable	H Configurable		
AJSC	AJSB	Steel for General Structure	Black Oxide
AJSCM	AJSBM		Electroless Nickel Plating
AJSCS	-	SUS304	-



Part Number	Type	No.	H										Unit Price							
			Selectable					Configurable 1mm Increment	d	H <sub>1</sub>	T	W	P	H <sub>2</sub>	d <sub>1</sub>	H Selectable		H Configurable		
			AJSC	AJSCM	AJSCS	AJSB	AJSBM									AJSLC	AJSLCM	AJSLCS		
(H Selectable)	(H Configurable)	3	15	20	10~40	2.5	5	7	26	16	4	4								
		4	15	20		3.5	5	7	26	16	4	4								
		5	15	20		25	4.5	6	9	32	20	5	6							
		6	15	20		25	5.5	6	9	32	20	5	6							
		8	20	25		30	40	7.5	8	12	38	26	6	7						
		10		25	30	40	9.5	10	16	50	32	9	9.5							
		12		25	30	40	11.5													
		16		25	30	40	15.5	11	19	65	40	12	11.5							


Ordering Example Part Number - H  
AJSCM8 - 20

**Side Mounting T Compact**



RoHS 10

Type		Material	Surface Treatment
H Selectable	H Configurable		
AJSCC	AJSCCM	SS400	Black Oxide
AJSCCS	-		Electroless Nickel Plating
		SUS304	-



Part Number	Type	No.	H Selection										Unit Price							
			Selectable					Configurable 1mm Increment	d	H <sub>1</sub>	T	W	P	H <sub>2</sub>	d <sub>1</sub>	AJSCC		AJSCCM		
			AJSCC	AJSCCM	AJSCCS															
		4	15	20	10~40	3.5	5	3	25	16	4	4								
		5	15	20		25	4.5	6	5	32	20	5	6							
		6	15	20		25	30	5.5	6	5	32	20	5	6						
		6	15	20		25	30	5.5	6	5	32	20	5	6						
		8	20	25		30	40	7.5	8	38	26	6	7							


Ordering Example Part Number - H  
AJSCC6 - 20

# Blocks for Adjusting Bolts / Adjusting Pins

## L-Shaped, L-Shaped Side Mounting


■Features: L-shaped Type has excellent stability. Available in two types (Standard, Side Mounting).

**Blocks for Adjusting Bolts L-Shaped Standard**



RoHS 10


Type		Material	Surface Treatment
H Selectable	H Configurable		
AJLC	AJLB	Steel for General Structure	Black Oxide
AJLCM	AJLBM		Electroless Nickel Plating



Part Number	Type	No.	H										Unit Price										
			Selectable					Configurable 1mm Increment	d	H <sub>1</sub>	T	W	P	L	B	T <sub>1</sub>	d <sub>2</sub>	d <sub>1</sub>	ℓ	AJLC			
			AJLC	AJLCM	AJLB	AJLBM																	
(H Selectable)	(H Configurable)	3	15	20	16~40	2.5	5	7	26	16	16	11	7	3.5	6	3.5							
		4	15	20		3.5	5	7	26	16	16	11	7	3.5	6	3.5							
		5	20	25		4.5	6	9	32	20	23	16	9	4.5	8	4.5							
		6	20	25		30	5.5	6	9	32	20	23	16	9	4.5	8	4.5						
		8	20	25		30	7.5	8	12	38	26	28	20	10	5.5	9.5	5.5						
		10		30	35	9.5	10	16	50	32	38	27											
		12		30	35	11.5							15	9	14.0	9							
		16		30	35	15.5	11	19	65	40	41	30											


Ordering Example Part Number - H  
AJLC10 - 30

**Blocks for Adjusting Bolts L-Shaped Side Mounting**



RoHS 10


Type		Material	Surface Treatment
H Selectable	H Configurable		
AJSLC	AJSLCM	Steel for General Structure	Black Oxide
AJSLCS	-		Electroless Nickel Plating
		SUS304	-



Part Number	Type	No.	H Selection										Unit Price						
			Selectable					Configurable 1mm Increment	d	H <sub>1</sub>	T	W	P	d <sub>1</sub>	T <sub>1</sub>	B	AJSLC		
			AJSLC	AJSLCM	AJSLCS														
(H Selectable)	(H Configurable)	3	15	20	16~40	2.5	5	7	26	16	4	4	5						
		4	15	20		3.5	5	7	26	16	4	4	5						
		5	15	20		25	4.5	6	9	32	20	6	5	6					
		6	15	20		25	5.5	6	9	32	20	6	5	6					
		8	20	25		30	40	7.5	8	12	38	26	7	8					
		10		25	30	40	9.5	10	16	50	32	9.5	7	9					
		12		25	30	40	11.5												
		16		25	30	40	15.5	11	19	65	40	11.5	8	10					


Ordering Example Part Number - H  
AJSLC8 - 40

**Adjusting Pins**



RoHS 10


Type	Material	Accessory
AJP	SUS304	Retaining Ring E Type (SUS304)
AJPB		-



Part Number	Type	D <sub>g6</sub>	L 1mm Increment	A	B	E	C	S	m Tolerance	N	d Tolerance	Unit Price	
												AJP	AJPB
												AJP	3
	4	-0.004	5 (10)~25	7	3	4.5	0.7	1.4	0.7	+0.1 0	2	+0.075 0	
	5	-0.012	10~30	8.5	4	5.5	1	2	0.7	+0.1 0	4	+0.075 0	
	6	-0.012	10~35	10	5	6.5	1.3	2.6	0.7	+0.1 0	5	+0.075 0	
	8	-0.005 -0.014	10~40	13	6	8.5	1.6	3.2	0.9	+0.14 0	3	+0.09 0	

For AJPB, L ≥ 10. S dimension is the maximum length of adjusting pins at 360° rotation by hex wrench.

Ordering Example Part Number - L  
AJP3 - 6



By machining oval shape on the moving part, fine adjustment of positioning is made possible by turning the adjusting. Adjusting pins have no function of fixing. AJP (Retaining Ring Type) cannot be fixed, but AJPB (Bolt Type) can be fixed by using double nuts.