


# Shaft Supports Side Mount (Machined)

## Standard / Slit


■ Features: Enables to mount on the plate side.

■ Standard



RoHS10


Type	Material	Surface Treatment	Accessory
SHQB	S45C	Black Oxide	Hex Socket Set Screw 1 pc.
SHQM	Equivalent	Electroless Nickel Plating	Hex Socket Set Screw 1 pc. (SUS)



25 / ( 63 / 1.5 )


Part Number Type	D	H Selection				L	H1	H2	T	L1	d	Set Screw M	Unit Price	
		25	30	40	50								SHQB	SHQM
SHQB SHQM	8	25	30			22	H+9			10				
	10	25	30				H+10							
	12	25	30			25	H+11	5	12	14	4.5	4		
	13	25	30				H+12							
	15	25	30	40		28	H+15			16				
	16	25	30	40										
	18	25	30	40	50	32	H+18	7	16	18	6.6	6		
	20	25	30	40	50									
	25		30	40	50	38	H+20			24				
	30		30	40	50	50	H+23							
	35		40	50	60									
	40		40	50	60		H+30			32	9	6		

■ Slit Type



RoHS10

Type	Material	Surface Treatment	Accessory
SHYB	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHYM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 1 pc. (SUS)
SHYS	SUS304	-	
SHYA	Aluminum Alloy	Clear Anodize	



25 / ( 63 / 1.5 )

Part Number Type	D	H Selection				L	H1	H2	T	L1	E	d	Tightening Screw M	d2	d1	l	C	Unit Price			
		20	25	30	40													SHYB	SHYM	SHYS	SHYA
SHYB SHYM SHYS SHYA	8	20	25	30		22	H+16			10	11										
	10	20	25	30																	
	12	20	25	30		25	H+18	5	12	14	13	4.5	M4 Depth 8	4.5	8	4.5	2				
	13	20	25	30																	
	15		25	30	40	28	H+20			16	15										
	16		25	30	40																
	18		25	30	40	50	32	H+26	7	16	18	18	6.6	M6 Depth 12	6.6	11	6.5				
	20		25	30	40	50															
	25		30	40	50	38	H+28			24	21										
	30		30	40	50	50	H+33			24											
	35		40	50	60																
	40		40	50	60		H+38			32	27	29	9	M Depth 16	9	14	9	3			

⚠ Values in ( ) are the T dimensions of SHYA (Aluminum).

Ordering Example: Part Number - H  
SHQM16 - 25  
SHYS12 - 30

Alterations: Part Number - HC  
SHQM16 - HC35.6  
SHYS40 - HC50.5


Alteration	Code	Spec.
Mounting Height	HC	Changes shaft mounting height. Change H to HC to specify height. Specify HC in 0.1mm increments. Specifiable Range: Hmin. < HC < Hmax. Ordering Code: HC35.6

# Shaft Supports Side Mount (Machined)

## Side Slit / Split


■ Features: Enables to mount on the plate side.

■ Side Slit



RoHS10

Type	Material	Surface Treatment	Accessory
SHUB	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHUM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 1 pc. (SUS)
SHUS	SUS304	-	
SHUA	Aluminum Alloy	Clear Anodize	




25 / ( 63 / 1.5 )

Part Number Type	D	H Selection				L	H1	H2	T	L1	E	d	Tightening Screw M	d2	d1	l	C	Unit Price			
		25	30	40	50													SHUB	SHUM	SHUS	SHUA
SHUB SHUM SHUS SHUA	8	25	30			26	H+7			16	8										
	10	25	30																		
	12	25	30			32	H+10	5	12	20	10	4.5	M4 Depth 8	4.5	8	4.5	2				
	13	25	30							21	10.5										
	15	25	30	40		34	H+12			23	11.5										
	16	25	30	40																	
	18	30	40	50		44	H+15	7	16	28	14	6.6	M6 Depth 12	6.6	11	6.5					
	20	30	40	50		50	H+18			34	17										
	25	30	40	50						36	18										
	30	40	50	60		70	H+21			48	24	9	M8 Depth 16	9	14	9	3				
	35	40	50	60			H+24														
	40	40	50	60		76	H+27			56	28										


⚠ Values in ( ) are the T dimensions of SHUA (Aluminum).

■ Split Type



RoHS10

Type	Material	Surface Treatment	Accessory
SHZB	S45C	Black Oxide	Hex Socket Head Cap Screw 2 pcs.
SHZM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 2 pcs. (SUS)
SHZS	SUS304	-	
SHZA	Aluminum Alloy	Clear Anodize	



25 / ( 63 / 1.5 )

Part Number Type	D	H Selection				L	H1	H2	T	L1	d	Tightening Screw M	d2	d1	l	C	Unit Price			
		25	30	40	50												SHZB	SHZM	SHZS	SHZA
SHZB SHZM SHZS SHZA	8	25	30			26	H+10			16										
	10	25	30																	
	12	25	30			32	H+10	5	12	20	4.5	M4 Depth 8	4.5	8	4.5	2				
	13	25	30							21										
	15	25	30	40		34	H+12			23										
	16	25	30	40																
	18	30	40	50		44	H+17	7	16	28	14	6.6	M6 Depth 12	6.6	11	6.5				
	20	30	40	50		50	H+20			34	17									
	25	30	40	50						36	18									
	30	40	50	60		70	H+30			48	24	9	M8 Depth 16	9	14	9	3			
	35	40	50	60			H+30													
	40	40	50	60		76	H+30			56	28									

⚠ Values in ( ) are the T dimensions of SHZA (Aluminum).

Ordering Example: Part Number - H  
SHUA10 - 25  
SHZM16 - 30

Alterations: Part Number - HC  
SHUS25 - HC31.5  
SHZM16 - HC35.6

Alteration	Code	Spec.
Mounting Height	HC	Changes shaft mounting height. Change H to HC to specify height. Specify HC in 0.1mm increments. Specifiable Range: Hmin. < HC < Hmax. Ordering Code: HC35.6