

Adjustable Draw Latches / Corner Draw Latches / Bar Latches / Cam Locks

Rotating Latches / Latches for Airtight Seals / Barrel Slide Bolt Latches / Slide Bar Latches

Adjustable Draw Latches RoHS10 **PKWSAJ1** 3-Through Ø5.3, Countersink Ø 10.3

PKWSAJ2 2-Through Ø5.3, Countersink Ø 10.3

Material SUS304 **Surface Treatment** -

| Part Number | No. | * Pull Force N (kgf) | Mass (g) | Unit Price 1 ~ 9 pc (s) | Volume Discount Rate 10~29 | 30~49 | 50~200 |
|-------------|-----|----------------------|----------|-------------------------|----------------------------|-------|--------|
| PKWSAJ | 1 | 588 (60) | 100 | | | | |
| | 2 | 588 (60) | 90 | | | | |

* Pull force is for 1mm pull distance.

Corner Draw Latches RoHS10 **PKBSK1** (Stainless Steel) In-line Catch Type

PKBSK2 (Stainless Steel) Right Angle Catch Type

Material SUS304 **Surface Treatment** Electrolytic Polishing

* The dimensions are for 0mm pull distance.

| Part Number | No. | * Pull Force N (kgf) | Mass (g) | Unit Price 1 ~ 9 pc (s) | Volume Discount Rate 10~19 | 20~100 |
|-------------|-----|----------------------|----------|-------------------------|----------------------------|--------|
| PKBSK | 1 | 44 (4.5) | 56 | | | |
| | 2 | | | | | |

* Pull force is for 1mm pull distance.

Bar Latches RoHS10 **HHMU**

Material SUS304 **Surface Treatment** Electrolytic Polishing

Cam Locks RoHS10 **LOCNL**

Part Name **Material** **Surface Treatment**

| | | |
|-----------------------|---------------|--------------------|
| Main Body | Zinc Die Cast | Chrome Plating |
| Hex Nut | SPCC | Trivalent Chromate |
| Lock Plate | SPCC | Tin-Cobalt Plating |
| Key (2 pcs. included) | SPCC | Tin-Cobalt Plating |

• Mass: 25g

Part Number **Operation Key Removal / Insertion** **Unit Price** **Volume Discount Rate**

| Type | No. | 1 ~ 9 pc (s) | 10 ~ 100 |
|-------|-----|--------------|----------|
| LOCNL | 1 | 1 Location | |
| | 2 | 2 Locations | |

Information

- The cam must turn right or left when locked, and must face upward when unlocked.
- Avoid applying external force to the cam when locked.
- Do not insert or remove the key while rotating. Insert/remove at a predetermined position.

Rotating Latches RoHS10 **LCR** **LCL**

Material SUS304 Equivalent **Surface Treatment** Buffing

The figure is for right-hand use.

| Part Number | L | Mass (g) | Unit Price |
|--------------------------|-----|----------|------------|
| LCR (For Right-hand Use) | 80 | 100 | |
| LCL (For Left-hand Use) | 100 | 130 | |

Ordering Example **Part Number** LCR80

Latches for Airtight Seals RoHS10 **LCAR** (For Right-hand Use) **LCAL** (For Left-hand Use)

Material SUS304 Equivalent **Surface Treatment** Buffing

The figure is for right-hand use.

| Part Number | No. | (L) | (L-1) | L2 | L3 | L4 | W | W1 | (H) | H1 | (H2) | H3 | P | P1 | P2 | (P3) | Mass (g) | Unit Price |
|---------------------------|-----|-----|-------|----|------|----|----|----|------|------|------|------|----|----|----|------|----------|------------|
| LCAR (For Right-hand Use) | 11 | 89 | 65.5 | 30 | 30 | 20 | 55 | 45 | 30 | 12.5 | 14.5 | 10 | 37 | 17 | 32 | 28 | 150 | |
| | 16 | 113 | 85.5 | 30 | 30 | 20 | 60 | 45 | 40 | 13 | 14.5 | 10 | 40 | 20 | 32 | 28 | 194 | |
| | 20 | 125 | 98 | 32 | 31.5 | 23 | 65 | 50 | 40 | 14 | 17 | 11 | 43 | 22 | 35 | 30 | 210 | |
| | 25 | 140 | 109 | 40 | 35 | 24 | 80 | 50 | 46.5 | 14.5 | 18 | 13 | 52 | 25 | 34 | 34 | 290 | |
| LCAL (For Left-hand Use) | 30 | 170 | 127 | 45 | 40 | 28 | 90 | 52 | 50.8 | 16.8 | 19 | 14.5 | 70 | 34 | 40 | 43 | 450 | |

Ordering Example **Part Number** LCAR16

Barrel Slide Bolt Latches RoHS10 **HHMT**

Material SUS304

Slide Bar Latches RoHS10 **HHMSQ**

Material SUS304

| Part Number | L | P | P1 | P2 | W | W1 | d | (S) | A | T | t | H | h |
|-------------|----|----|----|----|----|----|----|------|----|------|---|----|------|
| HHMSQ | 50 | 34 | 25 | 28 | 38 | 38 | 13 | 12.5 | 12 | 12.5 | 4 | 27 | 12 |
| | 65 | 47 | 31 | 32 | 45 | 45 | 15 | 15 | 15 | 13.5 | 5 | 28 | 12.5 |

| Part Number | N | Mass (g) | Unit Price | Volume Discount Rate |
|-------------|----|----------|------------|----------------------|
| HHMSQ | 50 | 3.5 | 7 | 58 |
| | 65 | 5 | 9 | 100 |

Ordering Example **Part Number** HHMT90 HHMSQ65