


Air Blow Nozzles



Threaded and Tapped											Height Adjusting Threaded, Tapped	Strut Clamp Mounting
Part Number		d	L		b	L Dimension Fixed		Unit Price	L Dimension Configurable		Unit Price	
Type	Nominal		L Fixed	L 1mm Increment		ABNZH, ABNML	ABNZS	ABNZHL, ABNMLL	ABNZSL			
(L Fixed)	5	1.0			0.5							
ABNZH		1.5	100	20 ~ 99	0.8	-	-	-	-			
ABNML		2.0	150		1.0	-	-	-	-			
ABNZS		2.5			1.5	-	-	-	-			
(L Configurable)		3.0			2.0	-	-	-	-			
ABNZHL	1	4.0			3.0	-	-	-	-			
ABNMLL		5.0	100	30~199	4.0	-	-	-	-			
ABNZSL		6.0	200		5.0	-	-	-	-			

2-Core Threaded										
Part Number		Nozzle Quantity	d	L		T R (PT)	b1	b2	Unit Price	
Type	Nominal			L Fixed	L 1mm Increment				L Fixed	L Configurable
(L Fixed) ABNKH	1	2	1.0	100	20-99	1/8	0.5	1.0		
(L Configurable) ABNXH			1.5				1.0	1.5		
			2.0				1.0	2.0		

Barbed Coupler										
Part Number		d	L		b	B	E	H	Unit Price	
Type	No.		L Fixed	L 1mm Increment					L Fixed	L Configurable
(L Fixed)	4	1.0	100	20~99	0.5	6.9	3.4	7		
ABNZT		1.5			0.8					
(L Configurable)	6	2.0			1	7	4.8	7		
ABNZTL		2.5			1.5					

Hose Nipple			d	L		b	B	E	H	Unit Price	
Part Number		L Fixed		L 1mm Increment	L Fixed					L Configurable	
Type	No.										
(L Fixed) ABNZP	4	1.7	100	20~99	0.9	8.5	6.5	7			
(L Configurable) ABNZPL	6	2.5			1.5	9.5	8.5	8			

ex Example



Position adjusted with Nut

ABNML