

Configurable Plates - Extra Super Duralumin
A7075P (Al-Zn-Mg Aluminum Alloy)





Table with 7 columns: Part Number, Type, Upper-Lower Surface Finish, Plate Thickness Tolerance, A, B, T. It details standard configurations for PP, PPF, and PPS plate types.

Two tables detailing tolerances: 1. Plate Thickness Tolerance (F, S) and 2. A, B Dimension Tolerance (F, S) across various length ranges.

Table detailing precision standards for thickness parallelism, flatness, and perpendicularity, including an ordering example: PP F Q M - 255 - 220 - 18.

Table detailing alterations for circumference chamfering and corner cuts, including a specification table for chamfering dimensions and a list of corner cut codes (CCA, CCB, CCC, CCD).

(Ex.) For PPF0M-255-220-18
A Dimension x Area Unit Price = Price

Large table showing part numbers and dimensions for PPF series plates, with columns for A, B, T, and various size ranges.

Large table showing part numbers and dimensions for PPS series plates, with columns for A, B, T, and various size ranges.

1mm Increment for T=5 ~ 7 of S (Surface)
* Except Surface Grinding