



# L-Shaped Welded Angles

Dimension Configurable




Type	Material
LSAW	A5052
LSUW	SUS304
T	Tolerance
10, 12	±1.0
15	±1.5



Part Number	A	B	Unit Price										
			LSAW10			LSAW12			LSAW15				
			L50-100	L101-150	L151-200	L50-100	L101-150	L151-200	L50-100	L101-150	L151-200	L201-250	L251-300
LSAW10 LSAW12 LSAW15	101-125	101-125	-	-	-	-	-	-	-	-	-	-	-
	126-150		-	-	-	-	-	-	-	-	-	-	-
	151-175		-	-	-	-	-	-	-	-	-	-	-
	176-200	-	-	-	-	-	-	-	-	-	-	-	-
	101-125	126-150	-	-	-	-	-	-	-	-	-	-	-
	126-150		-	-	-	-	-	-	-	-	-	-	-
	151-175		-	-	-	-	-	-	-	-	-	-	-
	176-200	-	-	-	-	-	-	-	-	-	-	-	-
	101-125	151-175	-	-	-	-	-	-	-	-	-	-	-
	126-150		-	-	-	-	-	-	-	-	-	-	-
	151-175		-	-	-	-	-	-	-	-	-	-	-
	176-200	-	-	-	-	-	-	-	-	-	-	-	-
101-125	176-200	-	-	-	-	-	-	-	-	-	-	-	
126-150		-	-	-	-	-	-	-	-	-	-	-	
151-175		-	-	-	-	-	-	-	-	-	-	-	
176-200	-	-	-	-	-	-	-	-	-	-	-	-	

Part Number	A	B	Unit Price										
			LSUW10			LSUW12			LSUW15				
			L50-100	L101-150	L151-200	L50-100	L101-150	L151-200	L50-100	L101-150	L151-200		
LSUW10 LSUW12 LSUW15	76-100	76-100	-	-	-	-	-	-	-	-	-		
	101-125		-	-	-	-	-	-	-	-	-		
	126-150		-	-	-	-	-	-	-	-	-	-	
	151-175	-	-	-	-	-	-	-	-	-	-	-	
	176-200	-	-	-	-	-	-	-	-	-	-	-	
	76-100	101-125	-	-	-	-	-	-	-	-	-	-	
	101-125		-	-	-	-	-	-	-	-	-	-	
	126-150		-	-	-	-	-	-	-	-	-	-	
	151-175	-	-	-	-	-	-	-	-	-	-	-	
	176-200	-	-	-	-	-	-	-	-	-	-	-	
	76-100	126-150	-	-	-	-	-	-	-	-	-	-	-
	101-125		-	-	-	-	-	-	-	-	-	-	-
126-150	-		-	-	-	-	-	-	-	-	-	-	
151-175	-	-	-	-	-	-	-	-	-	-	-	-	
176-200	-	-	-	-	-	-	-	-	-	-	-	-	
76-100	151-175	-	-	-	-	-	-	-	-	-	-	-	
101-125		-	-	-	-	-	-	-	-	-	-	-	
126-150		-	-	-	-	-	-	-	-	-	-	-	
151-175	-	-	-	-	-	-	-	-	-	-	-	-	
176-200	-	-	-	-	-	-	-	-	-	-	-	-	
76-100	176-200	-	-	-	-	-	-	-	-	-	-	-	
101-125		-	-	-	-	-	-	-	-	-	-	-	
126-150		-	-	-	-	-	-	-	-	-	-	-	
151-175	-	-	-	-	-	-	-	-	-	-	-	-	
176-200	-	-	-	-	-	-	-	-	-	-	-	-	

Long sides of A and B dims.	Perpendicularity k
76-150	0.10 or Less
151-200	0.15 or Less



Code CCA, CCB, CCC, CCD

Spec.	1mm Increment	
	Unit Price	Unit Price
1-3		
4-10		
11-20		
21-30		

Ordering Code (Ex.) When A and D are cut with C5 → CCA5-CCD5


Ordering Example Part Number - A - B - L  
LSAW10 - A120 - B120 - L150

Alterations Part Number - A - B - L - (CKC, SR, WR-etc.)  
LSAW10 - A120 - B120 - L150 - WR60


Alterations	Code	Spec.
	CKC	Both sides of dimension L are machined to be perpendicular to surface A. Ordering Code CKC
	SR	Gusset (t6mm) is welded at the center of dimension L. SR ≥ A/2 Ordering Code SR80 (Gusset Height = 80mm from Bottom Surface)
	WR	Two gussets (t6mm) are welded 2mm inside from both ends of dimension L. WR ≥ A/2 Ordering Code WR70 (Gusset Height = 70mm from Bottom Surface)

Note that, for some of the types shown here, order might be unable to be received by the MISUMI Indonesia offices.

# Lightweight Structural Steel (C-Shaped) / Metal Boxes / Box Stays



Type	Material
CASS	SS400
CASU	SUS304
CASH	A6063




CASH does not come with r1 or r2.

Part Number	Type	t	A-B	L 1mm Increment	T Tolerance	A		B		(r1)	(r2)	Unit Price							
						Tolerance	Tolerance	Tolerance	Tolerance			L30-100	L101-200	L201-400	L401-600	L601-800	L801-1000		
CASS		2.3	4020	30-1000	±0.25	40	±1.5	20	±1.5	4	2								
						80		40		8	2								
CASU		3	4020	30-1000	±0.4	40	±1.5	20	±1.5	4	2								
						80		40		4.5	3								
CASH		1.5	1515	30-1000	±0.23	15	±0.35	15	±0.35	-	-								
						25		25		-	-								
		2.5	2020		±0.23	20	±0.38	20	±0.38	-	-								
						50		25		-	-								
		3	4020		±0.23	40	±0.54	20	±0.38	-	-								
						60		30	±0.45	-	-								
		4	8040		±0.27	80	±0.92	40	±0.54	-	-								
						75		50		-	-								

Ordering Example Part Number - A-B - L  
CASH2 - 2525 - 400


Alterations Part Number - A-B - L - (NC)  
CASH2 - 2525 - 400 - NC3 - J10 - P80 - K3

Alteration	Code	Spec.
Hole Machining 	NC	NC: Applicable Bolt Size J: 1mm Increment P: Pitch in 1mm Increment K: Number of Holes Ordering Code NC3-J10-P80-K3
		3 M3 Ø3.5 4 M4 Ø4.5 5 M5 Ø5.5




Part Number	Type	A	L	Unit Price
75	75	100		
100	100	150		
150	150			

Ordering Example Part Number - L  
KBXS75 - 100



Part Number	Type	Nominal	A	P	Unit Price
75	76	35			
100	101	45			
150	151	55			



For rejecting foreign materials and defective parts