

Safety Protection Materials

D Type Rubber Bumpers

For hole machining type with D type rubber, suitable for use in places where adhesives cannot be used or tight mounting is necessary.

D Type Rubber Bumpers

Standard Type

Hole Type

*** Hole Machining Details**

Type	Screw Nominal Dia.	d	d1
PRGDS (Black)	5	6.0	11.0
PRGDSY (Stripe)	5	6.0	11.0
PRGDM (Black)	6	7.0	13.5
PRGDMG (Gray)	6	7.0	13.5
PRGDY (Stripe)	6	7.0	13.5
PRGDMY (Stripe)	6	7.0	13.5

Material: Main Body: Ethylene Rubber (EPDM), Adhesive Part: Acrylic Adhesives, Hardness: Shore A60

Standard Type

Part Number	L Selection (mm)	A	W	R1	R2	t	a	b	c	s	Weight (g)	Unit Price	
												PRGDS (Black)	PRGDSY (Stripe)
Compact Type PRGDS (Black) PRGDSY (Stripe)	100	14	20	R10	R7	3	2	18	2	0.3	19		
	500										95		
	1000										190		
	1500										285		
	2000										380		
Standard Type PRGDM (Black) PRGDMG (Gray) PRGDY (Stripe) PRGDMY (Stripe)	100	20	30	R15	R11	4	3	28	4	0.4	44		
	500										220		
	1000										440		
	1500										660		
	2000										880		

Peel off backing paper to adhere it to an object. Clean the mating surface off oil and dust.
 Can be cut with a utility knife. Adhesive Strength (180° Peeling): 16N/20mm Width (When affixed to SUS304) Properties: see the Ethylene Rubber of P.391

Hole Machining Charge

Part Number	L Selection (mm)	H specification (Number of Holes)	F specification (10mm Increment)	P specification (50mm Increment)	Hole Machining Charge																			
					1H	2H	3H	4H	5H	6H	7H	8H	9H	10H	11H	12H	13H	14H	15H	16H	17H	18H	19H	20H
PRGDS	500	1~5	F≥20	P≥100																				
PRGDSY	1000	1~10																						
PRGDM	1500	1~15																						
PRGDY	2000	1~20																						

Can be cut with a utility knife. Properties: see the Ethylene Rubber of P.391 Adhesive is not applied to Hole Type.

Ordering Example

Standard Type
 Part Number - L
 PRGDSY - 100

Hole Type
 Part Number - L - H - F - P
 PRGDY - 1000 - 5H - F100 - P150

The price of Hole Type is found by adding the Standard Type Unit Price to the Hole Machining Charge.
 (Ex.) Part Number - L - H - F - P
 PRGDY - 1000 - 5H - F100 - P150 >>
 (Standard Type Unit Price) + (Hole Machining Charge) = (Hole Type Unit Price)

Safety Protection Materials

D Type Rubber Bumpers for Corner / Safety Tapes

D Type Rubber Bumpers for Corner

Standard Type

PRGDSC (Compact)
 PRGDSCY (Compact, for Stripe)
 PRGDMC (Standard)
 PRGDMCY (Standard, for Stripe)

Hole Type

PRGDSCY (Compact)
 PRGDMCH (Standard)
 PRGDMCHY (Standard, for Stripe)

*** Hole Machining Details**

Type	Screw Nominal Dia.	d	d1
PRGDSCY (Compact)	5	6.0	11.0
PRGDMCH (Standard)	6	7.0	13.5
PRGDMCHY (Standard, for Stripe)	6	7.0	13.5

Material: Main Body: Ethylene Rubber (EPDM), Adhesive Part: Acrylic Adhesives, Hardness: Shore A60

Standard Type

Part Number	L Selection (mm)	A	W	R1	R2	t	a	b	c	s	Unit Price			Volume Discount Rate		
											1~3 pcs.	4~7 pcs.	8~30			
Compact Type PRGDSC (Black) PRGDSCY (Yellow)	70	14	20	R10	R7	3	2	18	2	0.3						
Standard Type PRGDMC (Black) PRGDMCY (Yellow)	100	20	30	R15	R11	4	3	28	4	0.4						

Peel off backing paper to adhere it to an object. Clean the mating surface off oil and dust. For orders larger than indicated quantity, please check with WOS.
 Can be cut with a utility knife. Adhesive Strength (180° Peeling): 16N/20mm Width (When affixed to SUS304) Properties: see the Ethylene Rubber of P.391


Hole Type

Part Number	L Selection (mm)	H Selection (mm)	A	W	R1	R2	t	a	b	c	s	Unit Price			Volume Discount Rate		
												1~3 pcs.	4~7 pcs.	8~30			
Compact Type PRGDSCY (Black) PRGDSCY (Yellow)	70	20	14	20	R10	R7	3	2	18	2	0.3						
Standard Type PRGDMCH (Black) PRGDMCHY (Yellow)	100	30	20	30	R15	R11	4	3	28	4	0.4						

Can be cut with a utility knife. Properties: see the Ethylene Rubber of P.391 Adhesive is not applied to Hole Type. For orders larger than indicated quantity, please check with WOS.

Ordering Example

Part Number - L - H
 PRGDSC - 70
 PRGDMCH - 100 - 30



Safety Tapes

PRTRT

Material Main Body: Polyethylene Foam, Surface: Polyethylene Print, Adhesive Part: Acrylic Adhesives

Part Number	Type	W Selection (mm)	L(m)	Unit Price
PRTRT		50 100	10	

L dimension is in meters.

Ordering Example

Part Number
 PRTRT50