

Shafts

Solid Type

■ Shaft length can be specified in 1mm increments. Stocked in fixed L dimensions.



Alterations	Code	Spec.
	RC	90-deg. Set Screw Flat at One Location <u>(Ordering Code)</u> RC10 <u>(Application Notes)</u> Only applicable to D=10 ~ 30. ❌ Not available in combination with WRC.
	WRC	90-deg. Set Screw Flats at Two Locations <u>(Ordering Code)</u> WRC10-Y10 <u>(Application Notes)</u> Only applicable to D=10 ~ 30. ❌ Not available in combination with RC. ❌ Orientation between two set screw flats is not coplanar.
	VC	V Groove at One Location <u>(Ordering Code)</u> VC8 <u>(Application Notes)</u> Applicable to D=6 or more ❌ Not available in combination with WVC.
	WVC	V Grooves at Two Locations <u>(Ordering Code)</u> WVC180-F8 <u>(Application Notes)</u> Applicable to D=6 or more ❌ Not available in combination with VC.
Keyway at one location 	KC	Keyway <u>(Ordering Code)</u> KC10-G10
Keyways at two locations 	WKC	KC10-C8 KC10-G10 <u>(Application Notes)</u> Only applicable to D=12, 16, 20, 25 and 30.

[illegible]

🚫 For D tolerance h5, add the relevant surcharge to the prices above.

Part Number		Unit Price							
Type	D	Min. L	L51	L101	L151	L201	L301	L401	
	3, 4, 5	50	100	150	200	300	400	500	
RSFJ	6								
	8								
	10								
	12								
	13								
	15								
	16								
	18								
	20								
	25								
	30								

Part Number		Unit Price							
Type	D	Min. L	L101	L201	L401	L601	L801	L1001	L1201
		100	200	400	600	800	1000	1200	1500
PSFG	6					-			
	8						-		
	10							-	
	12								-
	13								
	15, 16								
	18, 20								
	25								
	30								
	35								
	40								
	50								

Part Number		Unit Price							
Type	D	Min. L	L101	L201	L401	L601	L801	L1001	L1201
		100	200	400	600	800	1000	1200	1500
PSSFG	6								
	8								
	10								
	12								
	13								
	15, 16								
	18, 20								
	25								
	30								
	35								
40									
50									