




GRIP / MOUNTING BRACKET FOR AIR NIPPER


GRIP / MOUNTING BRACKET FOR AIR NIPPER

Y Line Clip



Material	Surface treatment
Aluminum product	Anodizing

MGMHC



- ① Single action: Ventilation is required when the product is gripped. No ventilation is required when the product is released.
- ② Double action: Ventilation is required when the product is either gripped or released.
- ③ This product's function is a pick-and-place component and is used for the installation of Grip fixtures. Note that it may not be compatible to assemble with other products.
- ④ When tightening, the gap is controlled to be less than 1mm.
- ⑤ The surface is anodized, and the color of the actual product may vary from the product picture.

Air pressure range (MPa)	Cylinder bore	
	16	20
Double action	0.25~0.6	
Single action	0.1~0.6	

Part Number			A	AA	B	BB	C	CC	D	DD	E	F	G	H	I	J
Type	Cylinder bore	Mode of action														
MGMHC	16	S (Single action)	3.9	23.6	16.2	15	44.6	30.6	62.5	22	22.6	16	4	7	7	24
	20	D (Double action)	4.5	27.6	21.7	18	55.2	42	78.7	32	28	20	5.2	9	8	30

Cylinder bore	K	L	M	N	O	P	S	T	U	V	W	X
16	M4×0.7	3.4	10.7	M4×0.7	16	M3×0.5	M5×0.8	M5×0.8	7	18.3	8	13
20	M5×0.8	4.3	15.7	M5×0.8	8.6	M4×0.7	M5×0.8	M5×0.8	7.5	22.2	10	15



Order

Part Number
MGMHC16S



Days to Ship


Quotation



Price


Quotation

Mounting Bracket for Air Nipper



Material	Surface treatment
Aluminum product	Anodizing

MSMBM



① Only suitable for Parallel Grips.

Part Number		A	B	C	D	E	F	G	H	I	J	Weight (g)
Type	No.											
MSMBM	10	3.2	6	2	23	16.4	12	18	14	4	M10×1	5
	16	4.2	7	3	30.6	23.6	15	22	15	5	M12×1	10
	20	5.5	7	4	42	27.6	18	32	15	5	M12×1	14



Order

Part Number
MSMBM10



Example



Days to Ship

Quotation



Price

Quotation

