


# Bushings for Locating Pins - High Hardness Stainless Steel

## Straight

For products uncovered by the e-Catalog Standards, see P.131.

Features: This product is much lower than, and can be delivered more quickly than the existing products.



Type			Material	Hardness
Dp6	Dm6	Dh7		
JBK	JBKM	JBKS	High Hardness Stainless Steel	35HRC~

D	p6	m6	h7
5	+0.020 +0.012	+0.012 +0.004	0 -0.012
7	+0.024 +0.015	+0.015 +0.006	0 -0.015
12	+0.029 +0.018	+0.018 +0.007	0 -0.018

### Straight



Part Number	P	L	R	Unit Price	Volume Discount Rate			
					1 ~ 19 pc(s)	20~49 pcs.	50~100 pcs.	101~300 pcs.
Type	D	0.1mm Increments	0.1mm Increments					
JBK (p6) JBKM (m6) JBKS (h7)	5	2.0~3.0	5.0~10.0	0.5				
	7	2.0~5.0	5.0~10.0					
	8	3.0~6.0	5.0~15.0					
	10	4.0~8.0	5.0~20.0					
	12	6.0~10.0	5.0~30.0					
	14	6.0~10.0	5.0~30.0					
15	8.0~12.5	5.0~40.0						



Ordering Example

Part Number			P	L
Type	D			
JBKM	8	-	5.9	12.0
JBKS	10	-	8.0	20.0

Alterations

Part Number			P	L	
Type	D				
JBKM	7	-	3.2	10.0	FC
JBKS	12	-	8.0	25.0	CRN

Alterations	Code	Spec.
Groove (for Adhesive Reservoir) 	FC	Adds an adhesive reservoir groove. D≥P+3: Applicable only when a wall of 1.5mm or thicker is remaining. Applicable only when L≥10.
Adhesive Groove Machining When L≤13.0 When L>13.0 	RS	Adds adhesive grooves. Number of O.D. Grooves When L≤13.0→Adds two grooves. When L>13.0→Adds three grooves. Ordering Code RS When D≤13, D-P≥3. When D≥14, D-P≥4. Not applicable to L<9.0.

Alterations	Code	Spec.
Radius R C Chamfered 	RN	Adds C Chamfering (0.5 or less) to R.
Radius R Square Corner 	CRN	Replaces R with square corner. Edge may be burred.