





Similar Component Page P1933

Comparison Points with Similar Products | Replacement Cycle (Reference) : 100,000 times Convenient package sale is available at a low price.

■ Double Tipped Probe Sold by the package (50 pcs./pkg.)



RNPA045



Part	M/Material	S/Surface Treatment
(1) Plunger	BeCu	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SWP	Gold Plating

■ Double Tipped Probe Sold by the package (50 pcs./pkg.)



RNPA051



Part	M/Material	S/Surface Treatment
(1) Plunger	BeCu	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SWP-A	Gold Plating

■ Double Tipped Probe Sold by the package (50 pcs./pkg.)



RNPA058



Part	M/Material	S/Surface Treatment
(1) Plunger	BeCu	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SWP	Gold Plating

■ Double Tipped Probe Sold by the package (50 pcs./pkg.)

RNPA085



Part	M/Material	S/Surface Treatment
(1) Plunger	BeCu	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SUS304	Gold Plating

Part Number		Tip Shape		Mounting Pitch (min)	Full Stroke	Spring Pressure (2/3 Stroke)	Allowable Current	Resistance	Replacement Cycle (Reference)	Unit Price (50 pcs./pkg.)
Type	No.	Left Side	Right Side							
RNPA	045	B J1	U, B, J U, J	0.6mm	1.1mm	23±7gf	1.0A	100mΩ	100,000 times	
RNPA	051	B J1	U, B, J U, J	0.65mm	1.1mm	22±5gf	0.5A	80mΩ	100,000 times	
RNPA	058	B J1	U, B, J U, J	0.8mm	1.1mm	25±5gf	1.0A	80mΩ	100,000 times	
RNPA	085	B J1	U, B, J U, J	1.0mm	1.1mm	31±6gf	5A	50mΩ	100,000 times	

Ordering Example Part Number (Type, No.) - L R  
RNPA045 - B J