


ミスミ

HSS DRILLS

ハイス鋼ドリル

●テーパシャンク/レギュラー -TAPERSHANK/REGULAR LENGTH-

TD



材質	HSS	ホモ処理
仕様	先端角 118°	レギュラー 28°~35° 再研磨

直径D	公差(h8)
8.5~9.8	0 -0.022
10.4~18	0 -0.027
18.5~30	0 -0.033
31~50	0 -0.039



◎ホモ処理=四三酸化鉄皮膜処理

一般鋼 (SS-SC材)	合金鋼 (SCM)	調質鋼 (~45HRC)	高硬度鋼 (50HRC~)	工具鋼 (SKD, SKS)	ステンレス鋼 (SUS)	鋳鉄 (FC, FCD)	アルミ (Al)	銅 (Cu)
--------------	-----------	--------------	---------------	----------------	--------------	--------------	----------	--------

○=適

型番 TD 1本単位

直径 D	溝長 ℓ	全長 L	MT No.	¥通常単価 10本以上お見積り		
				1本	2~4本	5~9本
8.5	75	156	1	1,670	1,580	1,330
9.8	87	168	1	2,190	2,080	1,860
10.4	87	168	1	2,760	2,620	2,210
10.5	87	168	1	2,010	1,910	1,610
11.8	94	175	1	2,860	2,720	2,290
12.5	101	182	1	2,260	2,150	1,810
12.8	101	182	1	3,010	2,860	2,410
13.5	108	189	1	2,260	2,150	1,810
14	108	189	1	2,350	2,230	1,880
14.2	114	212	2	3,330	3,160	2,660
14.5	114	212	2	2,630	2,500	2,100
15	114	212	2	2,700	2,570	2,160
15.5	120	218	2	2,820	2,680	2,260
15.8	120	218	2	3,790	3,600	3,030
16	120	218	2	2,960	2,810	2,370
16.5	125	223	2	3,210	3,050	2,570
17	130	228	2	3,400	3,230	2,720
17.5	130	228	2	3,550	3,370	2,840
17.7	130	228	2	4,810	4,560	3,840
18	130	228	2	3,750	3,560	3,000
18.5	130	228	2	3,850	3,660	3,080
19	130	228	2	4,030	3,830	3,220
19.5	140	238	2	4,280	4,070	3,420
19.8	140	238	2	5,690	5,400	4,550
20	140	238	2	4,430	4,210	3,540
20.5	145	243	2	4,520	4,290	3,620
21	145	243	2	4,700	4,470	3,760
21.2	145	243	2	8,500	8,080	6,800
21.5	150	248	2	4,890	4,650	3,910
22	150	248	2	5,020	4,770	4,020
22.5	155	253	2	5,240	4,980	4,190
23	155	253	2	5,430	5,160	4,340
23.5	155	276	3	5,930	5,630	4,740
24	160	281	3	6,160	5,850	4,930
24.5	160	281	3	6,430	6,110	5,140
25	160	281	3	6,610	6,280	5,290
25.5	165	286	3	6,840	6,500	5,470

直径 D	溝長 ℓ	全長 L	MT No.	¥通常単価 10本以上お見積り		
				1本	2~4本	5~9本
26	165	286	3	7,070	6,720	5,660
26.5	165	286	3	7,340	6,970	5,870
27	170	291	3	7,510	7,130	6,010
28	170	291	3	8,100	7,700	6,480
28.5	175	296	3	8,430	8,010	6,740
29	175	296	3	8,880	8,440	7,100
30	175	296	3	9,570	9,090	7,660
31	180	301	3	10,480	9,960	8,380
31.5	180	301	3	10,850	10,310	8,680
32	185	334	4	11,530	10,950	9,220
33	185	334	4	13,170	12,510	10,540
34	190	339	4	13,940	13,240	11,150
34.5	190	339	4	15,850	15,060	12,680
35	190	339	4	14,670	13,940	11,740
36	195	344	4	15,450	14,680	12,360
37	195	344	4	16,310	15,490	13,050
37.5	195	344	4	19,660	18,680	15,730
38	200	349	4	17,130	16,270	13,700
38.5	200	349	4	19,270	18,310	15,420
39	200	349	4	17,850	16,960	14,280
40	200	349	4	19,050	18,100	15,240
41	205	354	4	20,220	19,210	16,180
42	205	354	4	21,000	19,950	16,800
43.5	210	359	4	25,510	24,230	20,410
44	210	359	4	23,600	22,420	18,880
45	210	359	4	24,880	23,640	19,900
47	215	364	4	27,560	26,180	22,050
48	220	369	4	28,970	27,520	23,180
49	220	369	4	30,070	28,570	24,060
50	220	369	4	31,790	30,200	25,430



Order 注文例

TD 20

型番 直径(D)

切削条件 P.766



Delivery 出荷日

在庫品

巻末-3

◎ご希望によりPM6:00迄、当日出荷受付致します。