


ミスミ

HSS HIGH HERICAL REAMER

ハイス鋼ハイヘリカルリーマ (国内メーカー標準品)

● 右刃左ねじれ60°・テーパシャンク 0.1mm単位指定タイプ

HHHRT



刃径D	公差	刃径D	MT No.
4 ~ 6	+0.008 +0.004	4 ~ 14	1
6.1 ~ 10	+0.010 +0.006	14.1 ~ 23	2
10.1 ~ 30	+0.012 +0.007	23.5 ~ 30	3
刃径D	食付角θ		
4 ~ 30	1°30'		

型番 HHHRT

1本単位

刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥通常単価 1~4本	刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥通常単価 1~4本	刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥通常単価 1~4本	
4	5	22	110	3	4,010	13.3	10	45	180	3	7,090	17.7	10.5	50	210	4	11,790	
4.5	5	25	115	3	3,700	13.4	10	45	180	3	7,090	17.8	10.5	50	210	4	11,790	
5	6	25	115	3	3,700	13.5	10	45	180	3	5,930	17.9	10.5	50	210	4	11,790	
5.5	6	30	125	3	3,700	13.6	10	45	180	3	7,090	18	10.5	50	210	4	9,780	
6	7	30	125	3	3,700	13.7	10	45	180	3	7,090	18.1	10.5	50	210	4	12,480	
6.5	7	30	135	3	3,780	13.8	10	45	180	3	7,090	18.2	10.5	50	210	4	12,480	
7	7	30	135	3	3,780	13.9	10	45	180	3	7,090	18.3	10.5	50	210	4	12,480	
7.5	7	35	148	3	3,930	14	10	45	180	3	5,930	18.4	10.5	50	210	4	12,480	
8	8	35	148	3	3,930	14.1	10	46	200	3	7,700	18.5	10.5	50	210	4	10,400	
8.5	8	40	165	3	4,010	14.2	10	46	200	3	7,700	18.6	10.5	50	210	4	12,480	
9	8	40	165	3	4,010	14.3	10	46	200	3	7,700	18.7	10.5	50	210	4	12,480	
9.5	8	40	165	3	4,090	14.4	10	46	200	3	7,700	18.8	10.5	50	210	4	12,480	
10	10	40	165	3	4,090	14.5	10	46	200	3	6,400	18.9	10.5	50	210	4	12,480	
10.1	10	40	170	3	5,160	14.6	10	46	200	3	7,700	19	10.5	50	210	4	10,400	
10.2	10	40	170	3	5,160	14.7	10	46	200	3	7,700	19.1	10.5	55	220	4	13,250	
10.3	10	40	170	3	5,160	14.8	10	46	200	3	7,700	19.2	10.5	55	220	4	13,250	
10.4	10	40	170	3	5,160	14.9	10	46	200	3	7,700	19.3	10.5	55	220	4	13,250	
10.5	10	40	170	3	4,320	15	10	46	200	3	6,400	19.4	10.5	55	220	4	13,250	
10.6	10	40	170	3	5,160	15.1	10	47	205	3	9,860	19.5	10.5	55	220	4	11,020	
10.7	10	40	170	3	5,160	15.2	10	47	205	3	9,860	19.6	10.5	55	220	4	13,250	
10.8	10	40	170	3	5,160	15.3	10	47	205	3	9,860	19.7	10.5	55	220	4	13,250	
10.9	10	40	170	3	5,160	15.4	10	47	205	3	9,860	19.8	10.5	55	220	4	13,250	
11	10	40	170	3	4,320	15.5	10	47	205	3	8,170	19.9	10.5	55	220	4	13,250	
11.1	10	40	170	3	5,390	15.6	10	47	205	3	9,860	20	10.5	55	220	4	11,020	
11.2	10	40	170	3	5,390	15.7	10	47	205	3	9,860	20.5	10.5	55	220	4	11,710	
11.3	10	40	170	3	5,390	15.8	10	47	205	3	9,860	21	10.5	55	230	4	11,710	
11.4	10	40	170	3	5,390	15.9	10	47	205	3	9,860	21.5	10.5	55	230	4	12,560	
11.5	10	40	170	3	4,550	16	10.5	47	205	3	8,170	22	10.5	55	230	4	12,560	
11.6	10	40	170	3	5,390	16.1	10.5	47	205	3	10,780	22.5	10.5	55	230	4	13,560	
11.7	10	40	170	3	5,390	16.2	10.5	47	205	3	10,780	23	11	60	240	4	13,560	
11.8	10	40	170	3	5,390	16.3	10.5	47	205	3	10,780	23.5	11	60	240	4	14,790	
11.9	10	40	170	3	5,390	16.4	10.5	47	205	3	10,780	24	11	60	250	4	14,790	
12	10	40	170	3	4,550	16.5	10.5	47	205	3	9,010	24.5	11	60	250	4	16,100	
12.1	10	45	180	3	6,700	16.6	10.5	47	205	3	10,780	25	11	60	255	4	16,100	
12.2	10	45	180	3	6,700	16.7	10.5	47	205	3	10,780	25.5	11	60	255	4	17,560	
12.3	10	45	180	3	6,700	16.8	10.5	47	205	3	10,780	26	11	60	255	4	17,560	
12.4	10	45	180	3	6,700	16.9	10.5	47	205	3	10,780	26.5	11	60	255	4	19,560	
12.5	10	45	180	3	5,550	17	10.5	47	205	3	9,010	27	11	60	255	4	19,560	
12.6	10	45	180	3	6,700	17.1	10.5	50	210	3	11,790	27.5	11	60	260	4	21,560	
12.7	10	45	180	3	6,700	17.2	10.5	50	210	3	11,790	28	11	60	260	4	21,560	
12.8	10	45	180	3	6,700	17.3	10.5	50	210	3	11,790	28.5	11	60	260	4	22,260	
12.9	10	45	180	3	6,700	17.4	10.5	50	210	3	11,790	29	11	60	260	4	22,260	
13	10	45	180	3	5,550	17.5	10.5	50	210	4	9,780	29.5	11	60	260	4	23,030	
13.1	10	45	180	3	7,090	17.6	10.5	50	210	4	11,790	30	11	60	260	4	23,030	
13.2	10	45	180	3	7,090													

Order 注文例 HHHRT - 10.1 型番 刃径 (D)

Delivery 出荷日 3 日日出荷

切削条件 P.996

Price 価格 ■数量スライド価格 (※1円未満切捨て) お見積り

数量	1~4	5~9	10~49	50~99	100~
値引率	価格表	5%	10%	15%	