



STROKE END BLOCKS

STROKE END BLOCKS / END BLOCK CHAINS

— SQUARE HARDENED TYPE —



Catalog No.	Components				
	①	②	③	④	⑤
SBS	○	○	○	○	○
SBN	○	○	○	○	○
SEC	○	○	○	○	○



① ② M S45C
③ M SCM435
Strength class 12.9
JIS B 0205 Grade 2
④ Chain
⑤ C-ring JIS B 2804

Catalog No.	②		①		Base unit price 1 ~ 9 pieces			
Type	D	L	T	Color	Color	~ L80.0	L80.1 ~ L120.0	L120.1 ~
		0.1mm increments	5mm increments					
SBS ①②③④⑤	14	22.0 ~ 100.0	10 ~ 50	R (Red) Y (Yellow) N (Normal)	R (Red) Y (Yellow) N (Normal)			
	16							
	18							
	20							
	25							
	32							
	38							
50	25.0 ~ 200.0	10 ~ 50						
60		10 ~ 50						
								Quotation
SBN ②③	14	22.0 ~ 100.0	-	R (Red) Y (Yellow) N (Normal)	-			
	16							
	18							
	20							
	25							
	32							
	38							
50	25.0 ~ 200.0							
60								

③ Bolt size table									
D	d	M×P	ℓ	ℓ ₁	L	③			
14	7	M4	10	10	22.0 ~ 80.0	M4×20			
					80.1 ~ 100.0	M4×45			
16	7	M4	10	10	22.0 ~ 80.0	M4×20			
					80.1 ~ 100.0	M4×45			
18	8.5	M5	10	10	22.0 ~ 80.0	M5×45			
					80.1 ~ 100.0	M5×45			
20	10	M6	9	9	22.0 ~ 80.0	M6×20			
					80.1 ~ 100.0	M6×45			
					100.1 ~ 120.0	M6×65			
25	13	M8	12	8	22.0 ~ 80.0	M8×20			
					80.1 ~ 100.0	M8×45			
					100.1 ~ 120.0	M8×65			
					120.1 ~ 170.0	M8×90			
32	13	M8	12	8	22.0 ~ 80.0	M8×20			
					80.1 ~ 100.0	M8×45			
					100.1 ~ 120.0	M8×65			
					120.1 ~ 170.0	M8×90			
38	16	M10	16	9	25.0 ~ 80.0	M10×25			
					80.1 ~ 100.0	M10×50			
					100.1 ~ 120.0	M10×70			
					120.1 ~ 200.0	M10×100			
50	18	M12	18	7	25.0 ~ 80.0	M12×25			
					80.1 ~ 100.0	M12×50			
					100.1 ~ 120.0	M12×70			
					120.1 ~ 200.0	M12×100			
60	18	M12	18	7	25.0 ~ 80.0	M12×25			
					80.1 ~ 100.0	M12×50			
					100.1 ~ 120.0	M12×70			
					120.1 ~ 200.0	M12×100			

Catalog No.	①		Base unit price	
Type	D	T	1 ~ 9 pieces	
		5mm increments		
SEC ①④⑤	14	10 ~ 50	Quotation	
	16			
	18			
	20			
	25			
	32			
	38			
50	10 ~ 50			
60	10 ~ 50			
				Quotation


① N (Normal) → ② Black oxide (Fe₃O₄)

- Select colors for the body and spacer cap as needed in order to prevent incidents of forgetting to remove the spacer cap.
- Note: Be sure to specify the color of the spacer cap even when the colors of the body and spacer cap are the same.
- When used in cases such as (B), if the SBS body is 30 mm or less, the bolt head and spacer cap may interfere. Be sure that the spacer cap faces upward when it is used.



Order: Catalog No. - L - ② Color - T - ① Color
SBS 20 - 80.0 - Y - 20 - R
SBN 20 - 100.0 - R - 10 - Y
SEC 20

Days to Ship: Quotation

Price: Quotation



Alteration	Code	Spec.	1Code
	LKC	L dimension tolerance change L ₀ ^{+0.1} ⇔ ±0.01 When LKC is used, L dimension can be selected in 0.01mm increments. Resulting in variation of the finished L dimension of 0.005 or less. Can be used for SBS and SBN.	Quotation
	CHC	Change to standard chain length. L (CHC Selection) 22.0 ~ 49.9 50 100 200 50.0 ~ 99.9 100 200 100.0 ~ 200.0 200	Quotation
	RS	Change from the standard chain to a reinforced chain. Can be used for SBS20 ~ 60 and SEC20 ~ 60. Can be used for SBS and SEC when T ≥ 20. Length is 200 only.	Quotation
	NMC	Addition of a groove for height adjustment Can be used for SBS SBN with D32 or larger.	Quotation

① SKS93
② SCM435
Strength class 12.9
(JIS B 0205 Grade 2)



M×P	ℓ	d ₁	d ₂	h	Catalog No.		①		②			Base unit price 1 ~ 9 pieces		
					Type	A	B	L	Color	L1	L20.0	L40.1	L70.1	
								0.1mm increments		5mm increments	~ 40.0	~ 70.0	~ 100.0	
M4×0.7	8 12	8	5		SBVK	13	32 50	20.0 ~ 50.0	R (Red) Y (Yellow) N (Normal)	15 ~ 50				
M5×0.8	10 14	9.5	6	13		16	38 65	20.0 ~ 80.0		15 ~ 80				
M6×1.0	12 16	11	7		19	50 75	20.0 ~ 100.0		15 ~ 100					

Order: Catalog No. - B - ① - ② - L - Color - L₁
SBVK 16 - 38 - 50.0 - Y - 50

Price: Quotation

Alterations: Catalog No. - B - ① - ② - L - Color - L₁ - (LKC-LKP)
SBVK 16 - 38 - 50.00 - Y - 50 - LKC

Alteration	Code	Spec.	1Code
	LKC	L dimension tolerance change L ₀ ^{+0.1} ⇔ ±0.01 When LKC is used, L dimension can be selected in 0.01mm increments. Resulting in variation of the finished L dimension of 0.005 or less.	Quotation
	LKP	L dimension tolerance change L ₀ ^{+0.1} ⇔ ±0.01 When LKP is used, L dimension can be selected in 0.01mm increments. Resulting in variation of the finished L dimension of 0.005 or less.	Quotation

① SS400
② SPCC
③ SS400 (Lifting eye bolt M10×20) with nut


Catalog No.	T	Base unit price	
Type		1 ~ 9 pieces	
RSC	3 5	Quotation	

Order: Catalog No. RSC 3

Days to Ship: Quotation

Price: Quotation

Alterations: Catalog No. RSC 3

Example: 

* This is an example of a combination of RSC and stroke end block (P.967).