


ミスミ


PLAIN CLAMPS WITH TAP

ねじ穴付プレーンクランプ

MPC



■材質 S45C ■硬度 25~35HRC
■表面処理 四三酸化鉄皮膜



1個単位

型番	No.	タイプ	適合ボルト	A	B	C	D	ℓ	F	G	H	MXP (ネジ径×ピッチ)	重量 (g)	¥通常単価 1~4個
MPC	14	A	M14	100	38	19	16	28	23	16	16	14×2.0	440	2,280
		B		150					39				700	2,670
	16	A	M16	100					23				670	3,450
		B		150	50	25	22	36	32	19	18	16×2.0	1,110	3,810
		C		175					39				1,300	3,960
	18	A	M18	150					26				1,300	4,050
B		175		50	30	24	39	32	22	20	18×2.5	1,550	4,450	
	C		200					39				1,880	5,910	



MPC 14 - B
型番 No. タイプ



在庫品



数量スライド価格 (1円未満切捨て)

数量	1~4	5~9	10~19	20~29	30~
値引率	価格表	3%	5%	10%	


お見積り

ミスミ


DOUBLE END CLAMPS

ダブルエンドクランプ

DEC



■材質 S45C ■硬度 25~35HRC
■表面処理 四三酸化鉄皮膜



DEC 12
型番 No.



在庫品



数量スライド価格 (1円未満切捨て)

数量	1~9	10~19	20~29	30~39	40~
値引率	価格表	3%	5%	10%	


お見積り

ミスミ


U-CLAMPS WITH TAP

ねじ穴付U型クランプ

MUC



■材質 S45C ■硬度 25~35HRC
■表面処理 四三酸化鉄皮膜



MUC 18 - A
型番 M タイプ



在庫品



数量スライド価格 (1円未満切捨て)

数量	1~4	5~9	10~19	20~29	30~
値引率	価格表	3%	5%	10%	

お見積り